

**For
1~2 Surgery**

Megavac 2000A

AMALGAM COLLECTING SUCTION



DMEGA proudly introduce Megavac 2000A model which is sustainable solution for collecting amalgam waste in dental practice. Its high performance of amalgam separation rate over 95 % meets International standard of amalgam regulation. (ISO11143).

Specification

Main Voltage	230 VAC
Frequency	50 / 60Hz
Electrical power	0.55 / 0.63 Kw
Current consumption	3.8 / 4 Amp
Vacuum regulated	220 / 290 m bar
Suction motor rotation speed	2,900 / 3,440 rpm
Number of treatment units	1 ~ 2 Units
Weight	33 Kg
Dimensions	45(L) x 55(W) x 60(H)cm
Noise level	52db

